


DIAX2

MULTI DIRECTIONAL LAMINATES

CRUISE

DiAx 2 fait appel à notre toute dernière technologie en matière de scrim. La fibre est utilisée sans twist, sans aucun gaufrage, et bénéficie d'une géométrie parfaite, afin d'obtenir des matériaux performants, efficaces, tout en préservant la souplesse recherchée pour une bonne longévité.

Dans la pratique, l'utilisation de DiAx 2 permet de réduire les chutes tissus d'environ 15%, et de réduire le nombre de panneaux jusqu'à 70%, permettant ainsi la réalisation de voiles performantes, robustes et durables, mais à un coût raisonnable.



Specifications - DIAX2-TT Cruise: Taffeta-on-Taffeta

Style	Warp DPI	45 Degree DPI	65 Degree DPI	Total Fill DPI	Weight:		Film: mil
					gsm	smoz	
DIAX2-70TT Cruise	3000 Technora	2 x 2 1500 Technora	2 x 2 2280 HMT	3990 HMT	296	6.9	1.5
DIAX2-110TT Cruise	3000 Technora	2 x 2 1500 Technora	2 x 2 2280 HMT	8550 HMT	326	7.6	1.5
DIAX2-150TT Cruise	3000 Technora	2 x 2 1500 Technora	2 x 2 2280 HMT	13440 HMT	360	8.4	1.5

Specifications - DIAX2-PEN Cruise: Taffeta-on-Taffeta

Style	Warp DPI	45 Degree DPI	65 Degree DPI	Total Fill DPI	Weight:		Film: mil
					gsm	smoz	
DIAX2-50 PEN Cruise	2500 Polyester	2 x 2 840 Polyester	3 x 3 1000 Pentex	5000 Pentex	313	7.3	1.5
DIAX2-110 PEN Cruise	2500 Polyester	2 x 2 840 Polyester	3 x 3 1000 Pentex	10000 Pentex	338	7.9	1.5
DIAX2-150 PEN Cruise	2500 Polyester	2 x 2 840 Polyester	3 x 3 1000 Pentex	15000 Pentex	360	8.4	1.5

Tel : +33 (0) 251 130 540

Fax : +33 (0) 251 130 456

Email : info@bainbridgeint.fr

Applications - DIAX2-TT Cruise: Taffeta-on-Taffeta

Boat Length	Main	AP#1	#3
20-25	70TT	70TT	70TT
25-30	70TT	70TT	110TT
30-35	110TT	70TT	110TT
35-40	150TT	110TT	150TT

Applications - DIAX2-PEN Cruise: Taffeta-on-Taffeta

Boat Length	Main	AP#1	#3
up to 28	50PEN	50PEN	110PEN
up to 34	110PEN	50PEN	110PEN
up to 40	150PEN	110PEN	150PEN

Tel : +33 (0) 251 130 540

Fax : +33 (0) 251 130 456

Email : info@bainbridgeint.fr